

ABN 43 064 478 842

231 osborne avenue clayton south, vic 3169 PO box 1548, clayton south, vic 3169 t 03 9265 7400 f 03 9558 0875 freecall 1800 680 680 www.tmgtestequipment.com.au

Test & Measurement

sales

- rentals
- calibration
- repair
- disposal

Complimentary Reference Material

This PDF has been made available as a complimentary service for you to assist in evaluating this model for your testing requirements.

TMG offers a wide range of test equipment solutions, from renting short to long term, buying refurbished and purchasing new. Financing options, such as Financial Rental, and Leasing are also available on application.

TMG will assist if you are unsure whether this model will suit your requirements.

Call TMG if you need to organise repair and/or calibrate your unit.

If you click on the "Click-to-Call" logo below, you can all us for FREE!



Disclaimer:

All trademarks appearing within this PDF are trademarks of their respective owners.







CMA4000 Specifications

Display VGA LCD Display (8.4" color or 8.2" monochrome)

Mass Storage Up to 125 traces internal storage. Over 65,000 traces with optional hard drive.

Up to 180 traces for a standard 3.5 inch, 1.44 MB floppy disk.

Floppy disk drive comes standard

Stored Data Points up to 16,000

Group Refractive Index Setting 1.400000 - 1.699999

Loss Modes ORL, 2-point, 2-point LSA, dB/KM, dB/KM LSA, splice, reflectance

Trace Compare Modes Overlay, Delta Trace Compare, Align

Data Acquisition Real Time, Fast Scan, Medium Scan, Slow Scan, Timed Average (user selectable)

Information Output Trace display, FAS event table, integrated trace display with event information window, header page,

measurement parameters, ASCII report

Analysis High speed integrated fiber analysis

Vertical Scale Settings 0.125/0.25/0.5/1/2/4/8 dB (module dependent)

Horizontal Scale Settings 0.001 km/div. to 0.448 km/div @ 2 km; 0.001 km/div. to 57.304 km/div. @ 256 km (IOR = 1.5)

I/O Ports Standard: Integral alpha-numeric keyboard, (2) RS-232 Serial, (1) Parallel, VGA, Mouse,

External Keyboard Port

Language Capability English standard (others per request and may require hard drive option)

Physical Dimensions & Weight 9.5" H x 13.5" W x 3.75" D (24.1 x 34.3 x 9.5 cm) / 11.0 lbs. (4.9 kg)

Includes mainframe, battery and one module

Power

Power Supply Autoswitching 92-132 VAC, 47-63 Hz [weight 1.7 lbs. (.77 kg)]

184-264 VAC, 47-63 Hz

Battery Sealed Lead Acid Battery Pack [weight 1.4 lbs (0.63 kg)]

Battery Life up to 9 hours maximum per battery,

depending on operating mode

Recharge Time 1.5 - 2 hours

Environmental

Operation: AC Power Battery

 Temperature
 0°C to 45°C (32°F to 122°F)
 0°C to 40°C (32°F to 104°F)

 Humidity
 95% RH max., non-condensing
 95% RH max., non-condensing

Maximum Altitude 50,000 feet 50,000 feet

Storage:

Temperature -25°C to 60°C (-13°F to 140°F) Humidity 95% RH max., non-condensing

Maximum Altitude 50,000 feet

Optical Module Specifications [All measurements made using FC/SPC connectors at 25°C (77°F)]

| 413 | | 4415 | Models |
|------------------------------|---|--|--|
| 310 nm ± 20 nm | 1550 nm ± 30 nm | 1310 nm ± 20 nm | Center Wavelength |
| | | 1550 nm ± 30 nm | |
| inglemode 9/125µ | Singlemode 9/125µ | Singlemode 9/125µ | iber Type |
| 310 nm: 10 nm | 1550 nm: 10 nm | 1310 nm: 10 nm | pectral Width (RMS) |
| | | 1550 nm: 10 nm | |
| 310 nm: 30 dB | 1550 nm: 28 dB | 1310 nm: 30 dB | Dynamic Range ¹ |
| | | 1550 nm: 28 dB | (SNR = 1) |
| 310 nm: 3 meters (typical) | 1550 nm: 3 meters (typical) | 1310 nm: 3 meters (typical) | nitial Reflective Deadzone ² |
| | • • | 1550 nm: 3 meters (typical) | |
| 310 nm: 10 meters (typical) | 1550 nm: 12 meters (typical) | 1310 nm: 10 meters (typical) | nitial Non-Reflective Deadzone ² |
| | | 1550 nm: 12 meters (typical) | |
| | | 10 ns to 10μs | Pulsewidth |
| | 0.0001 mi | 0.0001 km; 0.1 meters; 0.001 kft, 1 ft, (| Distance Resolution |
| | dependent) | 0.25, 0.5, 1, 2, 4, 8, 16 meters (range d | Distance Sampling |
| | distance resolution ± index uncertainty | | Distance Accuracy |
| | , | 2/4/8/16/32/64/128/256 km | Distance Range Setting |
| | | 0.001 dB | oss Resolution |
| | e Safe) 21 CFR | Meets CDRH Class 1 Requirements (Eye | aser Safety |
| | e sale, Et et k | weeds epin class r nequirements (Eye | aser surecy |
| 423 | 4424 | 4425 | Models |
| 310 nm ± 20 nm | | 1310 nm ± 20 nm | Center Wavelength |
| 310 1111 2 20 1111 | 1330 11111 2 20 11111 | 1550 nm ± 20 nm | errer wavelenger |
| inglemode 9/125µ | Singlemode 9/125µ | Singlemode 9/125µ | iber Type |
| 310 nm: 10 nm | = | 1310 nm: 10 nm | pectral Width (RMS) |
| 31011111. 1011111 | 1330 11111. 10 11111 | 1550 nm: 10 nm | pectial width (MWS) |
| 310 nm: 36 dB | 1550 nm: 34 dB | 1310 nm: 36 dB | ynamic Range ¹ |
| 3 10 IIII. 30 GB | 1330 IIII. 34 UB | 1550 nm: 34 dB | (SNR = 1) |
| 210 mm; 2 motors (tymical) | 1FFO mm. 2 maters (tunical) | | nitial Reflective Deadzone ² |
| 310 nm: 3 meters (typical) | 1550 nm: 3 meters (typical) | 1310 nm: 3 meters (typical) | nitial Reflective DeadZone= |
| 240 40 (1 (1 (1 | 4550 42 (1 (1 (1 | 1550 nm: 3 meters (typical) | of the late of the state of the |
| 310 nm: 10 meters (typical) | 1550 nm: 12 meters (typical) | 1310 nm: 10 meters (typical) | nitial Non-Reflective Deadzone ² |
| | | 1550 nm: 12 meters (typical) | |
| | | 10 ns to 10μs | Pulsewidth |
| | | 0.0001 km; 0.1 meters; 0.001 kft, 1 ft, (| Distance Resolution |
| | | 0.25, 0.5, 1, 2, 4, 8, 16 meters (range d | Distance Sampling |
| | distance resolution ± index uncertainty | 0.0025% of distance measurement ± d | Distance Accuracy |
| | | 2/4/8/16/32/64/128/256 km | Distance Range Setting |
| | | 0.001 dB | oss Resolution |
| | e Safe) 21 CFR | Meets CDRH Class 1 Requirements (Eye | aser Safety |
| | | | |
| 534 | | 4438 | Models |
| 550 nm ± 20 nm | | 1550 nm ± 20 nm | Center Wavelength |
| | 1550 nm ± 20 nm | | |
| inglemode 9/125µ | | Singlemode | iber Type |
| 550 nm: 10 nm | | 15 nm | pectral Width (RMS) |
| | 1550 nm: 10 nm | | 1 |
| 550 nm: 40 dB | | 46.0 dB | Dynamic Range ¹ |
| | 1550 nm: 40 dB | | (SNR = 1) |
| 550 nm: 3.5 meters (typical) | | 3 meters | nitial Reflective Deadzone ² |
| | 1550 nm: 3.5 meters (typical) | | _ |
| 550 nm: 6 meters (typical) | 1310 nm: 6 meters (typical) | 5 meters | nitial Non-Reflective Deadzone ² |
| | 1550 nm: 6 meters (typical) | | |
| | 10 ns to 20µs (wavelength dependent) | | Pulsewidth |
| | | 0.0001 km; 0.1 meters; 0.001 kft, 1 ft, 0 | Distance Resolution |
| | | 0.25, 0.5, 1, 2, 4, 8, 16 meters (range de | Distance Sampling |
| | | 0.0025% of distance measurement ± dis | Distance Accuracy |
| | Stance resolution ± much uncertainty | 2/4/8/16/32/64/128/256 km | Pistance Range Setting |
| | | | |
| | o Safa) 21 CER | | |
| | C Juic, 21 CIN | wices Contricted interest (Eye | asci saicty |
| | e Safe) 21 CFR | 0.001 dB Meets CDRH Class 1 Requirements (Eye | Loss Resolution Laser Safety |

Notes:

^{1.} Subtract approximately 2 dB of range to 98% peak noise. Bellcore TR-TSY-000196 Issue 2 $\,$

^{2.} Using Bellcore TR-TSY-000196 Issue 2. Deadzones measured on -45 dB reflections.

| Models | 4442 | 4441 | 4440 |
|--|---|-----------------------------|------------------------------|
| Center Wavelength | 850 nm ± 20 nm | 1300 nm ± 20 nm | 850 nm ± 20 nm |
| | 1300 nm ± 20 nm | | |
| Fiber Type | Multimode | Multimode | Multimode |
| Spectral Width (RMS) | 850 nm: 10 nm | 1300 nm: 10 nm | 850 nm: 10 nm |
| | 1300 nm: 10 nm | | |
| Dynamic Range ¹ | 850 nm: 23 dB | 1300 nm: 26 dB | 850 nm: 23 dB |
| (SNR = 1) | 1300 nm: 26 dB | | |
| Initial Reflective Deadzone ² | 850 nm: 3.5 meters (typical) | 1300 nm: 3 meters (typical) | 850 nm: 3.5 meters (typical) |
| | 1300 nm: 3 meters (typical) | | |
| Initial Non-Reflective Deadzone ² | 850 nm: 6.5 meters (typical) | 1300 nm: 7 meters (typical) | 850 nm: 6.5 meters (typical) |
| | 1300 nm: 7 meters (typical) | | |
| Pulsewidth | 4 ns to 1µs (wavelength dependent | t) | |
| Distance Resolution | 0.0001 km; 0.1 meters; 0.001 kft, 1 | ft, 0.0001 mi | |
| Distance Sampling | 0.25, 0.5, 1, 2, 4, 8 meters (range dependent) | | |
| Distance Accuracy | 0.0025% of distance measurement ± distance resolution ± index uncertainty | | |
| Distance Range Setting | 2/4/8/16/32/64 km | | |
| Loss Resolution | 0.001 dB | | |
| Laser Safety | Meets CDRH Class 1 Requirements | (Eye Safe) 21 CFR | |

| Models | 4456 | 4457 |
|--|--|--|
| Center Wavelength | 850 nm ± 20 nm | 850 nm ± 20 nm |
| | 1300 nm ± 20 nm | 1300 nm ± 20 nm |
| | 1310 nm ± 20 nm | 1310 nm ± 20 nm |
| | 1550 nm ± 20 nm | 1550 nm ± 30 nm |
| Fiber Type | Multimode and Singlemode | Multimode and Singlemode |
| Spectral Width (RMS) | 850 nm: 10 nm | 850 nm: 10 nm |
| | 1300 nm: 10 nm | 1300 nm: 10 nm |
| | 1310 nm: 10 nm | 1310 nm: 10 nm |
| _ | 1550 nm: 10 nm | 1550 nm: 10 nm |
| Dynamic Range ¹ | 850 nm: 23 dB | 850 nm: 21 dB |
| (SNR = 1) | 1300 nm: 26 dB | 1300 nm: 24 dB |
| | 1310 nm: 21.5 dB | 1310 nm: 32 dB |
| _ | 1550 nm: 21 dB | 1550 nm: 30 dB |
| Initial Reflective Deadzone ² | 850 nm: 3.5 meters (typical) | 850 nm: 3.5 meters (typical) |
| | 1300 nm: 2.5 meters (typical) | 1300 nm: 2.5 meters (typical) |
| | 1310 nm: 3 meters (typical) | 1310 nm: 3 meters (typical) |
| _ | 1550 nm: 3 meters (typical) | 1550 nm: 3 meters (typical) |
| Initial Non-Reflective Deadzone ² | 850 nm: 6.5 meters (typical) | 850 nm: 6.5 meters (typical) |
| | 1300 nm: 7 meters (typical) | 1300 nm: 7 meters (typical) |
| | 1310 nm: 10 meters (typical) | 1310 nm: 15 meters (typical) |
| | 1550 nm: 12 meters (typical) | 1550 nm: 20 meters (typical) |
| Pulsewidth | 4 ns to 10 μs (wavelength dependent) | 4 ns to 10 µs (wavelength dependent) |
| Distance Resolution | 0.0001 km; 0.1 meters; 0.001 kft, 1 ft, 0.0001 mi | 0.0001 km; 0.1 meters; 0.001 kft, 1 ft, 0.0001 mi |
| Distance Sampling | 0.25, 0.5, 1, 2, 4, 8, 16 meters (range dependent) | 0.25, 0.5, 1, 2, 4, 8, 16 meters (range dependent) |
| Distance Accuracy | 0.0025% of distance measurement ± distance | 0.0025% of distance measurement ± distance |
| | resolution ± index uncertainty | resolution ± index uncertainty |
| Distance Range Setting | 2/4/8/16/32/64/128/256 km (wavelength dependent) | 2/4/8/16/32/64/128/256 km (wavelength dependent) |
| Loss Resolution | 0.001 dB | 0.001 dB |
| Laser Safety | Meets CDRH Class 1 Requirements (Eye Safe) 21 CFR | Meets CDRH Class 1 Requirements (Eye Safe) 21 CFR |

Notes:

- 1. Subtract approximately 2 dB of range to 98% peak noise. Bellcore TR-TSY-000196 Issue 2 2. Using Bellcore TR-TSY-000196 Issue 2. Deadzones measured on -45 dB reflections.

| Models | 4461 | 4462 |
|---|---|--|
| Center Wavelength | 1240 nm ± 6 nm | 1240 nm ± 6 nm |
| | | 1310 nm ± 20 nm |
| Fiber Type | Singlemode | Singlemode |
| Spectral Width (RMS) | 1240 nm: 15 nm | 1240 nm: 15 nm |
| 4 | | 1310 nm: 15 nm |
| Dynamic Range ¹ | 1240 nm: 36 dB | 1240 nm: 34 dB |
| (SNR = 1) | | 1310 nm: 34 dB |
| nitial Reflective Deadzone ² | 1240 nm: 3 meters (typical) | 1240 nm: 3 meters (typical) |
| | | 1310 nm: 3 meters (typical) |
| nitial Non-Reflective Deadzone ² | 1240 nm: 10 meters (typical) | 1240 nm: 10 meters (typical) 1310 nm: 10 meters (typical) |
| Pulsewidth | | 1310 IIII. 10 IIIetel3 (typical) |
| Distance Resolution | 0.0001 km; 0.1 meters; 0.001 kft, 1 ft, 0.0001 mi | 0.0001 km; 0.1 meters; 0.001 kft, 1 ft, 0.0001 mi |
| Distance Sampling | 0.25, 0.5, 1, 2, 4, 8, 16 meters (range dependent) | 0.25, 0.5, 1, 2, 4, 8, 16 meters (range dependent) |
| Distance Accuracy | 0.0025% of distance measurement ± distance | 0.0025% of distance measurement ± distance |
| · · · · · · · · · · · · · · · · · · · | resolution ± index uncertainty | resolution ± index uncertainty |
| Distance Range Setting | 2/4/8/16/32/64/128/256 km | 2/4/8/16/32/64/128/256 km |
| oss Resolution | 0.001 dB | 0.001 dB |
| aser Safety | Meets CDRH Class 1 Requirements (Eye Safe) 21 CFR | Meets CDRH Class 1 Requirements (Eye Safe) 21 CF |
| | | |
| Models | 4463 | 4464 |
| Center Wavelength | 1240 nm ± 6 nm | 1240 nm ± 6 nm |
| | 1550 nm ± 20 nm | 1625 nm ± 10 nm |
| iber Type | Singlemode | Singlemode |
| pectral Width (RMS) | 1240 nm: 15 nm | 1240 nm: 15 nm |
| 1 | 1550 nm: 15 nm | 1625 nm: 15 nm |
| Dynamic Range ¹ | 1240 nm: 36 dB | 1240 nm: 36 dB |
| (SNR = 1) | 1550 nm: 34 dB | 1625 nm: 36 dB |
| nitial Reflective Deadzone ² | 1240 nm: 3 meters (typical) | 1240 nm: 3 meters (typical) |
| | 1550 nm: 3 meters (typical) | 1625 nm: 3.5 meters (typical) |
| nitial Non-Reflective Deadzone ² | 1240 nm: 10 meters (typical) | 1240 nm: 10 meters (typical) |
| N. L | 1550 nm: 12 meters (typical) | 1625 nm: 15 meters (typical) |
| Pulsewidth | 0.0004 0.4 | 0.0004 0.4 0.004 ft. 4 ft. 0.0004' |
| Distance Resolution | 0.0001 km; 0.1 meters; 0.001 kft, 1 ft, 0.0001 mi | 0.0001 km; 0.1 meters; 0.001 kft, 1 ft, 0.0001 mi |
| Distance Sampling | 0.25, 0.5, 1, 2, 4, 8, 16 meters (range dependent) 0.0025% of distance measurement ± distance | 0.25, 0.5, 1, 2, 4, 8, 16 meters (range dependent) 0.0025% of distance measurement ± distance |
| Distance Accuracy | | |
| Distance Dance Catting | resolution ± index uncertainty | resolution ± index uncertainty 2/4/8/16/32/64/128/256 km |
| Distance Range Setting | 2/4/8/16/32/64/128/256 km | |
| oss Resolution aser Safety | 0.001 dB Meets CDRH Class 1 Requirements (Eye Safe) 21 CFR | 0.001 dB Meets CDRH Class 1 Requirements (Eye Safe) 21 CF |
| , | , , , , | , , , , |
| /lodels | 4471 | 4472 |
| enter Wavelength | 1625 nm ± 10 nm | 1310 nm ± 20 nm |
| | | 1625 nm ± 10 nm |
| | | c' l l |
| iber Type | Singlemode | Singlemode |
| * * | Singlemode 1625 nm: 10 nm | Singlemode 1310 nm: 10 nm |
| pectral Width (RMS) | <u>-</u> | 3 |
| pectral Width (RMS) Dynamic Range ¹ | <u>-</u> | 1310 nm: 10 nm 1625 nm: 10 nm 1310 nm: 36 dB |
| Fiber Type Spectral Width (RMS) Dynamic Range ¹ (SNR = 1) | 1625 nm: 10 nm 1625 nm: 36 dB | 1310 nm: 10 nm 1625 nm: 10 nm 1310 nm: 36 dB 1625 nm: 36 dB |
| opectral Width (RMS) Dynamic Range 1 (SNR = 1) | 1625 nm: 10 nm | 1310 nm: 10 nm 1625 nm: 10 nm 1310 nm: 36 dB 1625 nm: 36 dB 1310 nm: 3 meters (typical) |
| opectral Width (RMS) Oynamic Range 1 (SNR = 1) Initial Reflective Deadzone 2 | 1625 nm: 10 nm 1625 nm: 36 dB | 1310 nm: 10 nm 1625 nm: 10 nm 1310 nm: 36 dB 1625 nm: 36 dB |
| opectral Width (RMS) Oynamic Range 1 (SNR = 1) Initial Reflective Deadzone 2 | 1625 nm: 10 nm 1625 nm: 36 dB | 1310 nm: 10 nm 1625 nm: 10 nm 1310 nm: 36 dB 1625 nm: 36 dB 1310 nm: 3 meters (typical) 1625 nm: 4 meters (typical) 1310 nm: 10 meters (typical) |
| opectral Width (RMS) Dynamic Range 1 (SNR = 1) nitial Reflective Deadzone 2 nitial Non-Reflective Deadzone 2 | 1625 nm: 10 nm 1625 nm: 36 dB 1625 nm: 4 meters (typical) | 1310 nm: 10 nm 1625 nm: 10 nm 1310 nm: 36 dB 1625 nm: 36 dB 1310 nm: 3 meters (typical) 1625 nm: 4 meters (typical) |
| Oppectral Width (RMS) Oynamic Range 1 (SNR = 1) nitial Reflective Deadzone 2 nitial Non-Reflective Deadzone 2 | 1625 nm: 10 nm 1625 nm: 36 dB 1625 nm: 4 meters (typical) 1625 nm: 12 meters (typical) | 1310 nm: 10 nm 1625 nm: 10 nm 1310 nm: 36 dB 1625 nm: 36 dB 1310 nm: 3 meters (typical) 1625 nm: 4 meters (typical) 1310 nm: 10 meters (typical) 1625 nm: 12 meters (typical) |
| opectral Width (RMS) Oynamic Range 1 (SNR = 1) Initial Reflective Deadzone 2 Initial Non-Reflective Deadzone 2 Pulsewidth Distance Resolution | 1625 nm: 10 nm 1625 nm: 36 dB 1625 nm: 4 meters (typical) 1625 nm: 12 meters (typical) 0.0001 km; 0.1 meters; 0.001 kft, 1 ft, 0.0001 mi | 1310 nm: 10 nm 1625 nm: 10 nm 1310 nm: 36 dB 1625 nm: 36 dB 1310 nm: 3 meters (typical) 1625 nm: 4 meters (typical) 1310 nm: 10 meters (typical) 1625 nm: 12 meters (typical) |
| Opectral Width (RMS) Dynamic Range 1 (SNR = 1) Initial Reflective Deadzone 2 Initial Non-Reflective Deadzone 2 Pulsewidth Distance Resolution Distance Sampling | 1625 nm: 10 nm 1625 nm: 36 dB 1625 nm: 4 meters (typical) 1625 nm: 12 meters (typical) 0.0001 km; 0.1 meters; 0.001 kft, 1 ft, 0.0001 mi 0.25, 0.5, 1, 2, 4, 8, 16 meters (range dependent) | 1310 nm: 10 nm 1625 nm: 10 nm 1310 nm: 36 dB 1625 nm: 36 dB 1310 nm: 3 meters (typical) 1625 nm: 4 meters (typical) 1310 nm: 10 meters (typical) 1625 nm: 12 meters (typical) 0.0001 km; 0.1 meters; 0.001 kft, 1 ft, 0.0001 mi 0.25, 0.5, 1, 2, 4, 8, 16 meters (range dependent) |
| Opectral Width (RMS) Dynamic Range 1 (SNR = 1) Initial Reflective Deadzone 2 Initial Non-Reflective Deadzone 2 Pulsewidth Distance Resolution Distance Sampling | 1625 nm: 10 nm 1625 nm: 36 dB 1625 nm: 4 meters (typical) 1625 nm: 12 meters (typical) 0.0001 km; 0.1 meters; 0.001 kft, 1 ft, 0.0001 mi 0.25, 0.5, 1, 2, 4, 8, 16 meters (range dependent) 0.0025% of distance measurement ± distance | 1310 nm: 10 nm 1625 nm: 10 nm 1310 nm: 36 dB 1625 nm: 36 dB 1310 nm: 3 meters (typical) 1625 nm: 4 meters (typical) 1310 nm: 10 meters (typical) 1625 nm: 12 meters (typical) 0.0001 km; 0.1 meters; 0.001 kft, 1 ft, 0.0001 mi 0.25, 0.5, 1, 2, 4, 8, 16 meters (range dependent) 0.0025% of distance measurement ± distance |
| Opectral Width (RMS) Dynamic Range 1 (SNR = 1) Initial Reflective Deadzone 2 Initial Non-Reflective Deadzone 2 Pulsewidth Distance Resolution Distance Sampling Distance Accuracy | 1625 nm: 10 nm 1625 nm: 36 dB 1625 nm: 4 meters (typical) 1625 nm: 12 meters (typical) 0.0001 km; 0.1 meters; 0.001 kft, 1 ft, 0.0001 mi 0.25, 0.5, 1, 2, 4, 8, 16 meters (range dependent) 0.0025% of distance measurement ± distance resolution ± index uncertainty | 1310 nm: 10 nm 1625 nm: 10 nm 1310 nm: 36 dB 1625 nm: 36 dB 1310 nm: 3 meters (typical) 1625 nm: 4 meters (typical) 1310 nm: 10 meters (typical) 1625 nm: 12 meters (typical) 0.0001 km; 0.1 meters; 0.001 kft, 1 ft, 0.0001 mi 0.25, 0.5, 1, 2, 4, 8, 16 meters (range dependent) 0.0025% of distance measurement ± distance resolution ± index uncertainty |
| Spectral Width (RMS) Dynamic Range 1 | 1625 nm: 10 nm 1625 nm: 36 dB 1625 nm: 4 meters (typical) 1625 nm: 12 meters (typical) 0.0001 km; 0.1 meters; 0.001 kft, 1 ft, 0.0001 mi 0.25, 0.5, 1, 2, 4, 8, 16 meters (range dependent) 0.0025% of distance measurement ± distance | 1310 nm: 10 nm 1625 nm: 10 nm 1310 nm: 36 dB 1625 nm: 36 dB 1310 nm: 3 meters (typical) 1625 nm: 4 meters (typical) 1310 nm: 10 meters (typical) 1625 nm: 12 meters (typical) 0.0001 km; 0.1 meters; 0.001 kft, 1 ft, 0.0001 mi 0.25, 0.5, 1, 2, 4, 8, 16 meters (range dependent) 0.0025% of distance measurement ± distance |

| Models | 4473 |
|--|--|
| Center Wavelength | 1550 nm ± 20 nm |
| | 1625 nm ± 10 nm |
| Fiber Type | Singlemode |
| Spectral Width (RMS) | 1550 nm: 10 nm |
| | 1625 nm: 10 nm |
| Dynamic Range ¹ | 1550 nm: 34 dB |
| (SNR = 1) | 1625 nm: 36 dB |
| Initial Reflective Deadzone ² | 1550 nm: 4 meters (typical) |
| | 1625 nm: 4 meters (typical) |
| Initial Non-Reflective Deadzone ² | 1550 nm: 12 meters (typical) |
| | 1625 nm: 12 meters (typical) |
| Pulsewidth | |
| Distance Resolution | 0.0001 km; 0.1 meters; 0.001 kft, 1 ft, 0.0001 mi |
| Distance Sampling | 0.25, 0.5, 1, 2, 4, 8, 16 meters (range dependent) |
| Distance Accuracy | 0.0025% of distance measurement \pm distance resolution \pm index uncertainty |
| Distance Range Setting | 2/4/8/16/32/64/128/256 km |
| Loss Resolution | 0.001 dB |
| Laser Safety | Meets CDRH Class 1 Requirements (Eye Safe) 21 CFR |

Notes:

1. Subtract approximately 2 dB of range to 98% peak noise. Bellcore TR-TSY-000196 Issue 2

2. Using Bellcore TR-TSY-000196 Issue 2. Deadzones measured on -45 dB reflections.

Multi-Test Functions

Dual Source (441X and 442X optics only, factory installed)

 $1310/1550 \pm 20 \text{ nm}$ (except 4457 module 1550 ± 30 nm) Wavelength

Output -10 dBm (typical) Transmission Mode CW, 1 KHz and 2 KHz **Output Fiber** 9/125µm SM fiber **Optical Connector** Same as OTDR **Modes of Operation** CW, 1 KHz and 2 KHz Stability ± 0.2 dB (8 hours) Spectral Width Same as OTDR Safety Same as OTDR

Optical Meter (factory installed) +20 dBm meter option available

Detector Type 2 mm Ge PIN photodiode

Wavelength 800 - 1800 nm

+10 to -55 dBm or +20 to -45 dBm with AM460 filter Range

Calibrated Wavelengths 3 total: 850, 1310, 1550 **Universal Connector** Yes (use AM-430-xx adapter caps) Resolution 0.01 dB, dBm, 0.01% Watts

Store Reference Mode

Accuracy¹ ± 4% (± 0.18 dB) @ +5 dBm to -50 dBm

± 8% (± 0.36 dB) @ + 10 dBm to +5 dBm and

@ -50 dBm to -55 dBm

 \pm 0.04 dB, \pm 5 dBm to \pm 50 dBm Linearity

Visual Fault Locator (field installed)

Wavelength 635 ± 10 nm Output 0 dBm **Transmission Mode** CW or 2 Hz **Output Fiber** 9/125µm, SM fiber

Optical Connector FC, SC, ST - fixed connector

IEC 825 Class 2, FDA (21 CFR 1040. 10 class 2) Safety

1. Specification applies to +10 dBm meter not to +20 dBm meter.

CMA4000 Optional Accessories (must be added as separate line item):

| TD-400 | Hard transit case | TD-459US | US style keyboard |
|----------|----------------------------------|----------|--------------------------------------|
| TD-410 | Deluxe soft case | TD-459GE | German CE style keyboard |
| TD-415 | Soft carry bag | TD-459FR | French CE style keyboard |
| TD-405 | Printer w/cable | TD-459SP | Spanish CE style keyboard |
| TD-309 | Printer paper (5 rolls/pack) | TD-459IT | Italian CE style keyboard |
| TD-409 | Case of paper (5 packs/case) | TD-30163 | Additional User's Manual |
| TD-453 | 12 v lead acid battery | TD-30162 | Additional Training Manual |
| TD-29621 | 12 v DC power adapter | TD-30711 | Parallel cable - DB25M to DB25M |
| TD-30710 | Serial cable DB9F to DB9F (null) | TD-30712 | Serial cable DB9F to DB9M (straight) |

CMA4000 Mainframe:

Control Unit:

P/N TD-14XXX PC-based modular platform

Standard Accessories:

- 8-inch VGA LCD display
- Multi-tasking operating system
- User's & Training Manuals
- 1 VGA port
- Internal memory (up to 140 traces)
- 1 carry strap
- AC adapter/charger
- AC line cord (choose style see below)
- 2 serial ports
- 1 parallel port
- 1 mouse port
- 1 PS/2 keyboard port
- 12 v rechargeable battery (qty 2)
- Floppy drive
- Built-in keyboard

AC Power Cord Options:

| TD-11685 | US power cord | TD-30362 | Australian power cord |
|----------|--------------------|----------|-----------------------|
| TD-30358 | Euro power cord | TD-30359 | UK power cord |
| TD-30361 | Italian power cord | TD-30360 | Swiss power cord |

OTDR/Source Connector Adapter:

Adapters for PC and Ultra Polish:

| UC-130-10 | Biconic | UC-130-35 | SMA 905/906 |
|-----------|-----------|-----------|---------------------|
| UC-130-15 | DIN 47256 | UC-130-40 | Diamond HP HMS-10 |
| UC-130-20 | D4 | UC-130-45 | Diamond HP HMS-0 |
| UC-130-25 | FC | UC-130-50 | Diamond HP-HMS-10/A |
| UC-130-30 | ST | UC-130-55 | SC |

Adapters for Angle Polish:

| UC-130-60 | FC NTT | UC-130-70 | DIN/HRL-10 |
|------------|----------------|-----------|----------------|
| UC-130-60A | FC Seiko Giken | UC-130-75 | ST |
| UC-130-65 | SC | UC-130-80 | Diamond E-2000 |

Meter Connector Adapter (select one when ordering power meter):

| AM-430-10 | Biconic | AM-430-50 | ST |
|-----------|---------------|------------|---------|
| AM-430-15 | D4 | AM-430-75 | VFO/PFO |
| AM-430-20 | SMA 906 | AM-430-85 | DIN |
| AM-430-25 | Diamond GFS-3 | AM-430-90 | SC |
| AM-430-45 | FC | AM-430-100 | FDDI |

Total care for networks

109 N. Genesee St.
Utica, NY 13502
1-315-797-4449
1-800-443-6154
fax: 1-315-798-4038